

Small Sample Adapter™

for rheological evaluation where sample volume is limited

Standard Sample Chamber with embedded temperature probe provides direct temperature measurement of sample



Disposable Sample Chamber (Requires SSA-DCU Water Jacket)



Complete system shows the DV2T Viscometer and Small Sample Adapter with Circulating Water Bath for temperature control.



12.

What's Included?

1. DV2T Viscometer
2. Choice of Brookfield SC4 Spindle*
3. Choice of Brookfield SC4 Sample Chamber*
4. Insulating Cap
5. Extension Link with Coupling Nut
6. Storage Case (not shown)

*Specify when ordering

Optional Accessories

7. Embedded RTD temperature Probe in Chamber
8. SC4-13RD-100 (100/box) Disposable Sample Chambers Requires special water jacket
9. SC4-27D-100 (100/box) (p48) Disposable Spindles (p48)
10. SSA-DCU Special Water Jacket and SC4-13RD Disposable Chambers
11. SSA27D-13RD-100 Includes SSA-DCU (Chambers above) plus SC4-27D Disposable Spindles (100/box)
12. Temperature Bath (p33-35)
13. EZ-Lock Spindle Coupling (100/box)

For more info on Small Sample Adapter Accessory Kits visit our website.

The Small Sample Adapter provides a defined geometry system for accurate viscosity measurements at precise shear rates. Consisting of a cylindrical sample chamber and spindle, the Small Sample Adapter is designed to measure small sample volumes of 2 to 16 mL, and easily attaches to all standard AMETEK Brookfield Viscometers/Rheometers.

明頂科技有限公司

TEL.07-552-6160 FAX.07-586-6000

<https://www.mding.com.tw>

mding.s090602@msa.hinet.net